

SRT192RMBP



★★★★★ 5.0 (1) [Write a review](#)



Extended-run battery systems provide flexible runtime to critical Smart-UPS applications.
Includes: Installation guide, Warranty card



Technical Specifications

Output

Battery Output Voltage	192V
------------------------	------

Batteries & Runtime

Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Stand alone battery stack
Expected Battery Life (years)	3 - 5
RBC Quantity	2
Battery blocks per string	--

Physical

Maximum Height	5.1inches (130mm, 13.0CM)
Maximum Width	17.0inches (432mm, 43.2CM)
Maximum Depth	26.88inches (682mm, 68.27CM)
Rack Height	3U
Net Weight	200.2lbs. (91.0KG)
Shipping weight	232.1lbs. (105.5KG)
Shipping Height	16.54inches (420mm, 42.0CM)
Shipping Width	23.63inches (600mm, 60.0CM)
Shipping Depth	39.38inches (1000mm, 100.0CM)
Color	Black
Units per Pallet	1.0

[Back to top](#)



Environmental

Operating Temperature	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 (no %)
Operating Elevation	0-10000ft (0-3000meters)
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (no %)
Storage Elevation	0-50000ft (0-15000meters)

Conformance

Approvals	OSHDP
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Proposition 65 Warning	Available in Documentation tab

Back to top

