

# SpaceLogic Thermostat

## TH900 Series for PTAC, Fan Coil, Heat Pump & Gas/Oil Furnace Applications

TH903-P-W, TH903-ZP-W, TH903-ZPM-W, TH907-P-W, TH907-ZP-W, TH907-ZPM-W, TH907-P-B, TH907-ZP-B, TH907-ZPM-B



### Product Description

The TH900 Series thermostats are optimized for office building, hotel and residential terminal HVAC control.

The TH900 Series is ideal for PTAC, Fan Coil, Heat Pump and Gas/Oil Furnace applications.

These models are available in two housing finishes: optimum (black glass display with capacitive buttons on a black or white base) or medium (white glass display with mechanical buttons on a white base).

The TH900 Series is a wall surface mount device that is easy to operate. These thermostats feature microprocessor-based controls and large LCD screens which display operation status (cooling, heating and auto), fan speed, room temperature and set-point.

### Specifications

Heat stages	1 stage
Cool stages	1 stage
Sensing element	Digital temperature sensor
Accuracy	±0.5°C@0 to 50°C (±1°F@32 to 122°F)
Set-point range	5 to 35°C (41 to 95°F)
Display range	0 to 50°C (32 to 122°F)
Display resolution	0.5°C (1°F)

Operating temp.	0 to 50°C (32 to 122°F)
Operating humidity	0 to 95 % RH (non-condensing)
Storage temp.	-20 to 60°C (-4 to 140°F)
Storage humidity	0 to 90 % RH (non-condensing)
PIR detection	120° (±60°)
PIR detection distance	10m at 0°, 5m at 60°, 5m at -60°
Power consumption	Standby < 0.5W
Power supply	24 VAC @ 50/60Hz or 24 VDC
Terminal cable	14 AWG to 18 AWG solid or stranded wire
Load rating	3A resistive, 1A inductive, 1A pilot duty
Protection class	IP 30
Housing	Flame-retardant PC
Dimensions	120 x 120 x 26.5mm (4.72 X 4.72 X 1.04 in.)
Pollution degree	Pollution Degree 2
Operation type	Type 1.B
Control purpose	Operating control
Control construction	Independently mounted control for flush mounting
Impulse voltage	330V

USA: +1 888-444-1311  
Europe: +46 10 478 2000  
Asia: +65 6484 7877  
www.schneider-electric.com

**Schneider Electric**

© 2020 Schneider Electric. All rights reserved. All trademarks are owned by Schneider Electric Industries SAS or its affiliated companies. Schneider Electric, 35 rue Joseph Monier, F - 92500 Rueil-Malmaison June 2020 F-28128-2 nk

### Specifications (cont.)

Regulatory Information	
Agency approvals	FCC CFR 47 Part 15 Subpart B Class B RSS 247
	ICES-003:issue 6
	UL 60730-1
	UL 60730-2-9
	CAN/CSA-E60730-1
RoHS compliance	CAN/CSA-E60730-2-9
	European Conformance CE:
	IEC/EN 60730-1
REACH compliance	IEC/EN 60730-2-9
	2011/65/EU
2015/863/EU	


### Precautions

- This product is not intended for life or safety applications.
- Do not install this product in hazardous or classified locations.
- Read and understand the instructions before installing the product.
- Turn off all power supplying equipment before working on it.
- The installer is responsible for conformance to all applicable codes.
- External housing may be cleaned with a damp cloth if it becomes dirty. Do not use any cleaning agent, especially alcohol.


If this product is used in a manner not specified by the manufacturer, the protection provided by the product may be impaired. No responsibility is assumed by the manufacturer for any consequences arising out of the use of this material.

### Dimensions mm (in.)

#### TH907 Series



#### TH903 Series



© 2020 Schneider Electric. All rights reserved. All trademarks are owned by Schneider Electric Industries SAS or its affiliated companies. Schneider Electric, 35 rue Joseph Monier, F - 92500 Rueil-Malmaison

### Installation

#### Location

Select a location about 1.5m (5ft.) above the floor with good air circulation at average temperature. Indoor use only. Do not mount thermostat where it may be affected by:

- Drafts or dead spots behind doors or in corners
- Hot or cold air from ducts
- Radiant heat from sun or appliances.
- Concealed pipes or chimneys
- Unheated (un-cooled) areas behind the thermostat
- If Zigbee equipped, do not install near other RF sources/ transmitters
- When the thermostat is equipped with PIR, consider view angle, range characteristics, and mounting position for proper coverage

#### Mounting


The HVAC thermostat is typically mounted on a standard double-gang (4 x 4) junction box. The installation kit provides a Smart Wall Mounting Plate. If mounted on a single-gang box, use the two central holes of the Smart Wall Mounting Plate.

To mount the HVAC thermostat, complete the following steps:


- Position the Smart Wall Mounting Plate as shown in Figure 1.
- Ensure the Smart Mounting Plates are oriented to follow the marking that says "This side up". Snap them together, ensuring all 4 corner snap hooks are attached, then attach them to the junction box using the supplied screws.
- Use wire nuts to connect the Power/HVAC and other low voltage signal wiring harness to the power and heat pump/valve/fan control signal wires within the electrical box. See the pre-defined commissioning document for application-specific wire connections.
- To connect the unit to the input power and the relays to the loads, plug the pre-wired power/ HVAC and other signals harness connector into the female receptacle at the back of the unit (H1/H2/H3).

- Hook the tabs at the top rear of the unit housing into the matching depressions at the top of the Smart Mounting Plate and rotate the bottom of the housing toward the wall until it snaps into place.
- Secure the housing to the Smart Mounting Plate with the two small captive screws at the bottom of the housing.
- Apply power to the unit by closing the applicable supply breaker. After connecting power, OFF mode (factory default setting) will appear on the LCD display.

Figure 1. Assembly, exploded view



### Wiring



#### H1 White Connector: 24 VAC Power/HVAC Signals

Pin	Name	Color	Typical Function
1	RH	Brown	24 VAC (dedicated to heating power)
2	RC	Violet	24 VAC (dedicated to cooling/fan power)
3	G3	Grey	Fan speed 3 (high)
4	Y	Yellow	Cooling output (HVAC), compressor output (heat pump) or cold water valve (FCU)
5	-	-	Not connected
6	C	Black	Common
7	W/O/B	Blue	Heating output (HVAC), reversing valve (heat pump) or hot water valve (FCU)
8	G2/W2	White	Fan speed 2 (medium) / stage 2 heat (heat pump with aux. heating)
9	R	Red	24 VAC or 24 VDC (dedicated to product power)
10	G1	Green	Fan speed 1 (low)

#### H2 White Connector: Low Voltage Signals

Pin	Name	Color	Typical Function
1	AI	White	Not connected, reserve for future use
2	GND	Black	Ground
3	NC	None	Not connected
4	AUX2	Yellow	Auxiliary input 2, connects to Balcony Door/ External Occupancy sensor with dry contact output, two transitions to activate

Pin	Name	Color	Typical Function
5	AUX1	Blue	Auxiliary input 1, connects to key card/window switch with dry contact output. Use normal close/normal open configuration to activate.
6	12V	Red	12 VDC. Connects to external AUX1 or AUX2 switch/sensor with dry contact output.

#### H3 White Connector: Low Voltage Signals

Pin	Name	Color	Typical Function
1	B	White	RS485 DATA-
2	A	Red	RS485 DATA+
3	GND	Black	Ground

#### S1 Black Switch: Modbus Address Settings\*

Pin	Signal	Typical Function
1	X <sub>1</sub>	X <sub>1</sub> =1 if switch is ON, X <sub>1</sub> =0 if switch is OFF
2	X <sub>2</sub>	X <sub>2</sub> =1 if switch is ON, X <sub>2</sub> =0 if switch is OFF
3	X <sub>3</sub>	X <sub>3</sub> =1 if switch is ON, X <sub>3</sub> =0 if switch is OFF
4	X <sub>4</sub>	X <sub>4</sub> =1 if switch is ON, X <sub>4</sub> =0 if switch is OFF
5	X <sub>5</sub>	X <sub>5</sub> =1 if switch is ON, X <sub>5</sub> =0 if switch is OFF
6	-	Not connected


\*Modbus Address= X<sub>1</sub>\*2<sup>0</sup> + X<sub>2</sub>\*2<sup>1</sup> + X<sub>3</sub>\*2<sup>2</sup> + X<sub>4</sub>\*2<sup>3</sup> + X<sub>5</sub>\*2<sup>4</sup>  
Default address is 0. Adjust address range from 1-31 using S1, enable Modbus and set baud rate in the User Setup setting (see User Guide for details).


### Wiring Diagrams

Note: Prior to beginning an installation, use the HVAC Wire Harness Templates at the end of this document to identify the wires/signals coming out of the 4x4 box and to determine which wires are connected to which wires on the thermostat. These templates provide a quick and easy 'cheat sheet' to capture property-specific wiring requirements.


If you have technical questions, please contact the Schneider Electric Customer Care Center in your country (see schneider-electric.com/contact).

#### Generic FCU/Conventional HVAC: 24 VAC







Heat Pump O (HpO) Single-Stage Heat: 24 VAC



Heat Pump B (HpB) Two-Stage Heat:24 VAC



Heat Pump O (HpO) Two-Stage Heat: 24 VAC



Thermostat - Typical HVAC Applications

Unit Relay	4-Pipe FCU (3 Fan, 1 Heat/Cool)	2 Pipe FCU (3 Fan, Cool Only)	Heat Pump (3 Fan, 1 Stage Heat)	Heat Pump (2 Fan, 2 Stage Heat)	PTAC (2 Fan with Heat Strip)
G3	High fan	High fan	High fan	High fan	High fan
G2/W2	Medium fan (G2)	Medium fan (G2)	Medium fan (G2)	Second stage heat (W2)	NC
G1	Low fan	Low fan	Low fan	Low fan	Low fan
Y	Cool Signal	Cool Signal	Compressor (Y)	Compressor (Y)	Compressor (Y)
W/O/B	Heat Signal (W)	NC	Reversing valve (O/B)	Reversing valve (O/B)	Heat Signal (W)

User Interface  
User Setup Setting Mode  
When unit is OFF (but powered), long press and hold the FAN button for 15 seconds to enter the user setup setting table. See user guide for details.

Installer Setup Setting Mode  
When unit is OFF (but powered), long press and hold the F/C button for 15 seconds. Release the F/C button after the backlight flash. Press the UP button within three seconds to enter the installer setup setting table. See the user guide for details.

Protection Mode  
When Frost Protection and High Temperature Protection is enabled, the measured ambient temperature is continuously monitored to ensure it does not exceed the High Temperature Protection setpoint or fall below the Frost Protection setpoint. An LCD and alarm indication alerts the user that the temperature exceeds the upper or lower limit. See the user guide for details.

Normal Operation Mode  
When a button is pressed by the user, the device will display the system modes and the tempera-

the setpoint is changed (defaults back to Auto mode) or the M button is pressed.

During normal operation, the measured ambient temperature is continuously monitored to ensure it does not exceed the High Temperature Protection setpoint if High Temperature Protection is enabled. Similarly, the measured ambient temperature is monitored to ensure it does not fall below the Frost Protection setpoint if the Frost Protection configuration is enabled.

Protection Modes  
The Frost Protection and High Temperature Protection modes can be enabled or disabled. When enabled, their setpoints are configurable, as described below.

- Frost Protection (low temperature) can be enabled or disabled. When enabled, its setpoint ranges from 5 to 15°C (41 to 59°F). Default is 5°C (41°F). If Frost Protection is enabled and the measured ambient temperature is lower than its Frost Protection limit, then even when the device is OFF, heating will turn on automatically, as indicated on the LCD. Heating will turn off when the ambient temperature reaches the setpoint + 2°C (4°F).
- High Temperature Protection can be enabled or disabled and its setpoint ranges from 25 to 35°C (77 to 95°F). The default is 35°C (95°F). If High Temperature Protection is enabled and the measured ambient temperature is higher than its setpoint limit, then even when the device is OFF, cooling will turn on automatically as indicated on the LCD. Cooling will turn OFF when the ambient temperature decreases to the High Temperature Protections setpoint minus 2°C (4°F).





If the low temperature exceeds the display range of 0°C (32°F), this will be indicated with 'LO' on the LCD.

If the high temperature exceeds the display range 50°C (122°F), this will be indicated with 'HI' on the LCD.


If the on-board temperature sensor is not operating correctly (if it is open or short), 'Er' will be displayed on the LCD.

ture. When the unit is not in use for more than 15 seconds, the LCD and button backlight will turn off or brightness will be minimized.

ECO Mode  
ECO mode minimizes energy consumption when a room is unoccupied and the device is ON. It allows for quick resumption when people return to the room. When the room is unoccupied, the device reverts back to ECO mode.

Button Lock and Unlock Mode  
When the unit is ON, press and hold the  button for 15 seconds. Release the  button after the Lock icon flickers. Then press the UP button within three seconds to activate the button lock. The Lock icon will appear on the LCD. When the button lock is activated, press and hold the  button for 15 seconds. Release the  button after the Lock icon flickers, then press the UP button within three seconds to deactivate the button lock. The Lock icon will disappear from the LCD.

Interface Navigation



No.	Item	Function
1	F/C button	Single button press toggles °F / °C
2	LCD	Displays temperature, system mode icon (cool/heat/auto), lock icon, fan speed icon, etc.
3	Mode button	A short press of this button cycles through the system modes*.
4	On-board occupancy sensor (PIR)	PIR detects whether a room is occupied or unoccupied. PIR detection angle: 120° (+/-60°), PIR detection distance: 10 m at 0°, 5 m at 60°, 5 m at -60°.
5	Down button	Single button press decreases auto mode setpoint by 0.5°C (1°F).
6	Up button	Single button press increases auto mode setpoint by 0.5°C (1°F).

7	Fan button	Single button press toggles between pre-set fan speeds and fan auto mode.
---	------------	---

\*Mode screens displayed depend on user configuration settings. For a list of available modes, see the "System Mode Selection" section of this document.

Normal Operation Mode  
Setting the Fan Speed

A short press of the FAN button toggles between pre-set fan speeds and fan auto mode.

- AUTO - Fan operates in low, medium or high speed as needed (and can be disabled in configuration). Setting the fan to AUTO allows the blower to operate off and on intermittently in time with the heating or cooling system.
- FAN LOW - Fan operates in low speed.
- FAN MEDIUM – Fan operates in medium speed
- FAN HIGH – Fan operates in high speed


A fan setting of ENABLE/DISABLE can also be set in the User Setup Settings menu.

- ENABLE - Fan blower continues to run after the system is turned off (OFF mode). Allows for manual switching of fan speeds (LOW/MEDIUM/HIGH/OFF).
- DISABLE - Fan turns off after the system is turned off (OFF mode).

System Mode Selection  
Touchscreen Models



Note: Default modes are OFF and Auto. Additional modes can be enabled by the user.



Note: Default modes are OFF and Auto. Additional modes can be enabled by the user.


The default modes displayed by TH900 Series thermostats are OFF and Auto. Other available mode options include OFF/Auto/Heat/Cool, OFF/Heat Only and OFF/Cool Only. In order to access these modes, the user must first enable them within the Installer Setup Setting Mode settings.

With a short press of the MODE button, the thermostat will cycle between OFF > Auto by default modes. In each of these modes, the contents of the display change accordingly. Note that Auto, Heat Only and Cool Only have identifying icons displayed above (touchscreen version) or to the left of the temperature (pushbutton version).

- In Auto mode, the measured ambient temperature is compared to the set point. Temperature control is achieved by setting the fan speed to automatic and engaging the heating or cooling valves.
- When the fan is operating under automatic control, the applicable fan on/off is chosen automatically based on the temperature difference necessary to achieve the air temperature set point.
- If the user selects the fan to run in low speed via the fan button, then temperature control is delegated to the heating control and cooling control. The fan is no longer modulated until

HVAC Wire Harness Templates

Use the wire harness templates below to note your wiring connections.



Regulatory Compliance  
FCC

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference

in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

Industry Canada  
This device complies with Industry Canada licence-exempt RSS standard(s) . Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

WEEE Directive 2012/19/EC  
Waste Electrical and Electronic Equipment Directive

Dispose of this device separately from household waste at an official collection point. Professional recycling protects people and the environment against potential negative effects.

User Guide Link  
Use the URL or QR code below to access the user guide for this product.



<https://portal2.schneider-electric.com/>