



# NetShelter SX 42U 750mm Wide x 1070mm Deep Networking Enclosure with Sides Black

## AR3140

Call for More Information 800-800-4272

- NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.
- Includes: Baying hardware, Key(s), Keyed-alike doors and side panels, Leveling feet, Mounting hardware, Pre-installed casters, Side panels, Vertical cable managers

Physical	
Maximum Height	78.39inches (1991MM, 199.1CM)
Maximum Width	29.53inches (750MM, 75.0CM)
Maximum Depth	42.13inches (1070MM, 107.0CM)
Rack Height	42U
Net Weight	343.09lbs. (155.95KG)
Shipping weight	370.0lbs. (168.18KG)
Shipping Height	83.39inches (2118MM, 211.8CM)
Shipping Width	33.5inches (850MM, 85.09CM)
Shipping Depth	45.5inches (1156MM, 115.6CM)
Color	Black
Maximum Mounting Depth	32.25inches (819.0MM, 81.92CM)
Minimum Mounting Depth	11.0inches (279.0MM, 27.94CM)
Front Door	16.0gauge
Vertical Posts	16.0gauge
Rear Door	16.0gauge
Roof	18.0gauge
Side Panels	18.0gauge
Units per Pallet	1.0
Rack Width	19"
Weight Capacity (static load)	3750.0lbs. (1704.55KG)

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

### Physical

Weight Capacity (dynamic load)	2250.0lbs. (1022.73KG)
--------------------------------	------------------------

### Environmental

Protection Class	IP 20
------------------	-------

### Conformance

Approvals	UL 2416, UL 60950-1
Standard warranty	5 year repair or replace

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOL	Available in Documentation tab

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.