

V321





⚠ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH


- Follow safe electrical work practices. See NFPA 70E in the USA, or applicable local codes
- This equipment must only be installed and serviced by qualified electrical personnel.
- Read, understand and follow the instructions before installing this product.
- $\bullet \quad \text{Turn off all power supplying equipment before working on or inside the equipment.} \\$
- Use a properly rated voltage sensing device to confirm power is off.
 DO NOT DEPEND ON THIS PRODUCT FOR VOLTAGE INDICATION

Failure to follow these instructions will result in death or serious injury.

NOTICE

- This product is not intended for life or safety applications.
- Do not install this product in hazardous or classified locations.
- The installer is responsible for conformance to all applicable codes.
- · Mount this product inside a suitable fire and electrical enclosure.

DIMENSIONS



V321

20A DPST Enclosed Relay With Dual HOA Switches

Installer's Specifications

4006 - 4006 / 400 - 10405
-40°C to 40°C (-40° to 104°F)
10-90% non condensing
Electrical (at rated current): 100,000 cycles
Mechanical (unpowered): 10,000,000 cycles
LED ON=energized
14" (356mm) min.
UL1015; Coil: 18AWG; Contacts: 12AWG
277VAC RMS
UL508 enclosed device listing, pollution degree 2

INSTALLATION

Disconnect and lock out all power sources before beginning the installation.

- Using the threaded nipple, connect the relay to the desired enclosure through a knock out hole.
- 2. Secure with the conduit nut provided.
- 3. Connect coil:
 - Choose the coil common lead (white with yellow stripe) and connect it to the common (-) source termination point.
 - Choose either the low voltage (24VAC/DC, white with blue stripe) or high voltage (120VAC, white with black stripe) lead, depending on the application requirements, and connect it to the (+) source termination point.*

NOTE: When connecting the control side of this device (#18 wires) to power line circuits, provide current limiting at 7 amps max.

4. Connect relay contacts:

Output #1


 Choose the two relay N.O. (solid orange) leads and connect to the switched load.

Output #2

- Choose thetwo relay N.O. (solid brown) leads and connect to the switched load.
- 5. Secure the enclosure and reconnect power.
- * Isolate or insulate all non-terminated wires according to local electrical code requirements, i.e. wire nut.



WIRING COLOR CODES



CONTACT AND COIL SPECIFICATIONS


TYPICAL COIL PERFORMANCE Voltage Coil Current AC DC

Voltage	Coil C	urrent
	AC	DC
24V	120mA	64mA
120V	84mA	-


CONTACT RATINGS		
Resistive	20A@240VAC	
	8A@28VDC	
	14A@14VDC	
Motor	120VAC, 1HP	

WIRING EXAMPLE

Nipple mount directly to a panel




Nipple mount to a 2x or 4x electrical box



* Isolate any unused wires, e.g. wire nut.

HOA POSITIONS





HAND OFF

AUTO

ND Up position: contacts are closed.

F Middle position: contacts are open.

Down position: control system actuates the contacts.